



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH227NRK 800A/2P HD Fusible Safety Switch W/Neut 240V Nema

Eaton Corp

Catalog Number	DH227NRK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, Enhanced Visible Blade, 800 A, Nema 3R, Painted Galvanized Steel, Class L, Two-Pole, Three-Wire, 240 V, Max HP: 100, 250 HP (3PH @ STD Fuse/Time Delay), (4)#1/0-(4)750 Kcmil Al
Weight per unit	165.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	800
Material	Galvanized Steel
media	Yes
Poles	2
Voltage Rating	240V

Dimensions and Weight

Depth	65
Height	13
Width	27

Descriptions

Description	800A/2P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA
extra long description	ETN DH227NRK 800A/2P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, Enhanced visible blade, 800 A, NEMA 3R, Painted galvanized steel, Class L, Two-pole, Three-wire, 240 V, Max Hp: 100, 250 hp (3PH @ Std fuse/time delay), (4)#1/0-(4)750 kcmil Al
Product Type	800A/2P HD FSBL Sfty SW W/Neut 240V N3R
Special Features	Enhanced visible blade

Manufacturer Information

Brand	Eaton
GTIN	00782113589671
Manufacturers Part Number	DH227NRK
UPC	782113589671



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 165

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier