



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH324NGK 200A/3P HD Fusible Safety Switch W/Neut 240V Nema1

Eaton Corp

Catalog Number	DH324NGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Fused Safety Switch, 200 A, Nema 1, Painted Steel, Class H, Neutral, Three-Pole, Four-Wire, 240 V, Max HP: 15, 25/ 15, 60/ 40 HP (1, 3PH @STD/TD/250 VDC), #6-250 Kcmil Cu/Al
Weight per unit	43.0 (lbs/each)
Product Category	Fusible Heavy Duty Safety Swit

Features

amperage rating	200
dimensions	30.0000 IN X 18.0000 IN X 9.5000 IN
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	240V

Dimensions and Weight

Depth	30
Height	9.5
Width	18

Descriptions

Description	200A/3P HD FUSIBLE SAFETY SWITCH W/NEUT 240V NEMA1
extra long description	ETN DH324NGK 200A/3P HD FSBL Sfty S
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw fused safety switch, 200 A, NEMA 1, Painted steel, Class H, Neutral, Three-pole, Four-wire, 240 V, Max Hp: 15, 25/ 15, 60/ 40 hp (1,3PH @Std/TD/250 Vdc), #6-250 kcmil Cu/Al
Product Type	200A/3P HD FSBL Sfty SW W/Neut 240V N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113206684
Manufacturers Part Number	DH324NGK
UPC	782113206684



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Fusible safety switch

Packaging

Carton 1

Weight Per each 43

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 1

standard UL Listed, NEC 230.62 (C) Compliant Barrier