



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH365UGK 400A/3P HD NF Safety Switch 600V Nema 1

Eaton Corp

Catalog Number	DH365UGK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 400 A, Nema 1, Painted Steel, Non-Fusible, Three-Pole, Three-Wire, 125 At 240 Vac TD 3 PH, 250 At 480 Vac TD 3 PH, 350 At 600 Vac TD 3 PH, 50 At 250 VDC
Weight per unit	105.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	400
Material	Painted Steel
media	Yes
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	12.31
Height	44.31
Width	24.12

Descriptions

Description	400A/3P HD NF SAFETY SWITCH 600V NEMA 1
extra long description	ETN DH365UGK 400A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 400 A, NEMA 1, Painted steel, Non-Fusible, Three-pole, Three-wire, 125 at 240 Vac TD 3 Ph, 250 at 480 Vac TD 3 Ph, 350 at 600 Vac TD 3 Ph, 50 at 250 Vdc
Product Type	400A/3P HD NF Sfty SW 600V N1

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113207223
Manufacturers Part Number	DH365UGK
UPC	782113207223



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch

Packaging

Carton	1
Weight Per each	105

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Power Distribution and Controls
nema rating	1
standard	UL Listed,NEC 230.62 (C) Compliant Barrier