



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DH367URK 800A/3P HD NF Safety Switch 600V Nema 3R

Eaton Corp

Catalog Number	DH367URK
Manufacturer	Eaton Corp
Description	Eaton Heavy Duty Single-Throw Non-Fused Safety Switch, Single-Throw, 800A, Nema 3R, Painted Galvanized Steel, Non-Fusible, Three-Pole, Three-Wire, 500 At 480 Vac TD 3 PH, 500 At 600 Vac TD 3 PH
Weight per unit	158.0 (lbs/each)
Product Category	Non-Fusible Heavy Duty Safety

Features

amperage rating	800
Material	Galvanized Steel
media	Yes
Poles	3
Voltage Rating	600 V

Dimensions and Weight

Depth	14.07
Height	55.82
Width	26.37

Descriptions

Description	800A/3P HD NF SAFETY SWITCH 600V NEMA 3R
extra long description	ETN DH367URK 800A/3P HD NF Sfty Sw
Features	Eaton's heavy-duty safety switches provide a highly visible means of disconnect to help improve personnel safety and equipment protection. Additionally, they're Ideal for applications where reliable performance, safety, and service continuity are critical.
Long Description	Eaton Heavy duty single-throw non-fused safety switch, Single-throw, 800A, NEMA 3R, Painted galvanized steel, Non-Fusible, Three-pole, Three-wire, 500 at 480 Vac TD 3 Ph, 500 at 600 Vac TD 3 Ph
Product Type	800A/3P HD NF Sfty SW 600V N3R

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113589756
Manufacturers Part Number	DH367URK
UPC	782113589756

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Non-Fusible Safety Switch



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton 1

Weight Per each 158

Uses, Certifications, and Standards

Application Commercial / Institutional Buildings / Structures - Power
Distribution and Controls

nema rating 3R

standard UL Listed, NEC 230.62 (C) Compliant Barrier