



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## DH4X1C150 1-1/2" Hdpe W/Tape 150'

*Abb Installation Products, Inc*

Catalog Number	DH4X1C150
Manufacturer	Abb Installation Products, Inc
Description	Riser-Gard Fiber Optic Corrugated Conduit, Size 1-1/2 Inch, Outer Diameter 1.91 Inch, Inner Diameter 1.54 Inch, Wall Thickness 0.080 Inch, Length 150 Feet, Material PVC, Color Orange, With Pull Tape
Weight per unit	0.2200 (lbs/each)
Product Category	Non-Metallic Raceway & Accy.

### Features

Inside Diameter	1.54
outside diameter	1.91

### Material, Color, and Finish

Color	Orange
-------	--------

### Dimensions and Weight

Length	1800
--------	------

### Descriptions

Description	1-1/2" HDPE W/TAPE 150'
extra long description	ABB DH4X1C-150 1.5 INCH R/G ORANGE
Long Description	Riser-Gard Fiber Optic Corrugated Conduit, Size 1-1/2 Inch, Outer Diameter 1.91 Inch, Inner Diameter 1.54 Inch, Wall Thickness 0.080 Inch, Length 150 Feet, Material PVC, Color Orange, with Pull Tape
Product Type	1.5 Inch R/G Orange W/Tape
Special Features	UL Listed and is available with tape pre-installed

### Manufacturer Information

Brand	Carlton
GTIN	00791207203539
Manufacturers Part Number	DH4X1C-150
UPC	791207203539

### Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION MOTOR CONTROL
Type	Riser-Gard Flexible Raceway

### Trade Size

Trade Size	1-1/2 INCH
------------	------------

### Availability

minimum qty	150
-------------	-----



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	150
Weight Per foot	0.22

## Uses, Certifications, and Standards

Application	Riser-Gard is suitable for use in vertical runs in a shaft or between floors, as well as areas other than the plenum
standard	UL e151168