

# Eaton DK3400

Catalog Number: DK3400

Eaton Series C complete molded case circuit breaker, K-frame, DK, Complete breaker, Fixed thermal, Fixed magnetic trip, Three-pole, 400 A, 240 Vac, 250 Vdc, 65 kAIC at 240 Vac, 10 kAIC at 250 Vdc, Aluminum, Line and load, 50/60 Hz



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Series C complete molded case circuit breaker	DK3400
	<b>UPC</b>
	786679044155

<b>Product Length/Depth</b>	<b>Product Height</b>
14 in	6.5 in

<b>Product Width</b>	<b>Product Weight</b>
7 in	12.6 lb

<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## defaultTaxonomyAttributeLabel

### Amperage Rating

400 A

### Voltage rating

240 Vac, 250 Vdc

### Trip Type

Fixed thermal, fixed magnetic

### Circuit breaker type

DK

### Circuit breaker frame type

Complete breaker

### Series

Series C

### Terminals

Line and load

### Frame

K

### Frequency rating

50 to 60 Hz

### Terminal material

Aluminum

### Interrupt rating

10 kAIC at 250 Vdc

65 kAIC at 240 Vac

### Number of poles

Three-pole

## Resources

### Application notes

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

### Brochures

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Motor protection circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[StrandAble terminals product aid](#)

[Multi-wire lugs product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Breaker service centers](#)

### Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

### Drawings

[KD3 2D PDF](#)

[KD3 AutoCAD 2D Footprint \(mm\)](#)

[KD3 AutoCAD 2D Footprint](#)

[KD3 2D Drawing Xchange](#)

[KD3 3D Model Xchange](#)

[KD3 3D Inventor](#)

### Installation instructions

[Installation Instructions for DK, KDB, KD, HKD, KDC, KW, HKW, KWC, CKD, CHKD Circuit Breakers and Molded Case Switches](#)

[Instruction Leaflet for the KES 310+ Electronic Trip Unit](#)

### Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

### Specifications and datasheets

[Series C J-Frame molded case circuit breakers time current curves](#)

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)

[Eaton Specification Sheet - DK3400](#)

[Series C F-Frame molded case circuit breakers](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)