



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DSXF1LEDP250K 42W Led FLD 50K Wide DST KNKL MNT *Lithonia Lighting*

Catalog Number	DSXF1LEDP250K
Manufacturer	Lithonia Lighting
Description	Lith DSXF1 Led P2 50K M4 D-Series S
Weight per unit	8.2 (lbs/each)
Product Category	Led Floodlights

Features

Fixture Type	FLOODLIGHT
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Maximum Operating Temperature	25
pallet quantity	72
Shape	Rectangular
Voltage Rating	120 to 277
Warranty	5
Wattage	42

Material, Color, and Finish

Color	Bronze
color rendering index (cri)	70
Finish	Gloss
Lens Material	Glass
Style	CONTEMPORARY

Dimensions and Weight

Height	5
Length	15
Width	10

Descriptions

Description	42W LED FLD 50K WIDE DST KNKL MNT
Long Description	LITH DSXF1 LED P2 50K M4 D-Series S
Product Type	Floodlight
Special Features	The sleek design of the D-Series Floodlights reflects the embedded high performance LED technology. They are ideal for landscape, signage, accent, security and general area lighting in many commercial and residential applications.



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00190887243338
Manufacturers Part Number	DSXF1 LED P2 50K M4
UPC	190887243338

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	FLOODLIGHT

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight	9
Weight Per each	8.15

Uses, Certifications, and Standards

Application	Automotive & Parking, Education, Government, Healthcare, Hospitality, Manufacturing, Office & Banks, Power & Gas, Religious, Residential, Retail, Sports and Recreation, Transportation, Warehouses, Waters, Sewers & Dams
environmental conditions	OUTDOOR
Mounting	Pole Mount
standard	CSABAA, DLC Premium, DLC Standard