



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVSTVLA Diva DV 8A 0-10V 3WAY Light Almond

Lutron

Catalog Number	DVSTVLA
Manufacturer	Lutron
Description	Diva Dimmer - Gloss Finish, Fluorescent or Led Dimming With 0-10V Ballasts and Drivers, Single-Pole/3-Way, 120-277V/50MA/8A In Light Almond
Weight per unit	0.2600 (lbs/each)
Product Category	Lighting Dimmers

Features

amperage rating	8
Connection Type	Wire Leads
insulation	Plastic
media	Yes
Poles	1
Switch Type	Paddle Switch
Voltage Rating	120 to 277
Wattage	2216

Material, Color, and Finish

Color	Light Almond
Finish	Gloss

Dimensions and Weight

Size	4.69 x 2.94;119 x 75
------	----------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	DIVA DV 8A 0-10V 3WAY LIGHT ALMOND
extra long description	LUT DVSTV-LA DIVA 0-10 W/SWITCHING
Features	The Diva 0-10V dimmer switch is a simple solution is designed to match existing design style switches and accessories. Easily turn the lights on and off with a paddle switch, and use the slide control to adjust the lights to the perfect level. The new Diva 0 - 10-Volt dimmerswitch is a 0-10 VDC dimmer with 3-way functionality for 3rd party 0-10-Volt fixtures (LED and fluorescent), no separate power pack required. Coordinating wall plate sold separately.
Long Description	Diva Dimmer - Gloss Finish, Fluorescent or LED Dimming with 0-10V Ballasts and Drivers, Single-pole/3-way, 120-277V/50mA/8A in light almond
Product Type	Diva 0-10 W/Switching Box Light Almond
Special Features	Controls 0-10 V LED or fluorescent fixture loads, 50 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim.

Manufacturer Information

Brand	Lutron
GTIN	00784276099615
Manufacturers Part Number	DVSTV-LA
UPC	784276099615

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer, 3-way/single-pole

Packaging

Carton	1
Package	24
Weight Per each	0.26

Uses, Certifications, and Standards

Application	Lighting Control
Enclosure	Plastic
environmental conditions	Indoor use only
Mounting	WALLBOX
standard	UL, CSA