



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



DVSTVWH Diva DV 8A 0-10V 3WAY White

Lutron

| | |
|------------------|---|
| Catalog Number | DVSTVWH |
| Manufacturer | Lutron |
| Description | Dimmable Bulb, Paddle Switch, 120 to 277 V, 3 W, Fluorescent Lamp, Wall Mount, 2.94 In Length, 2.75 In Width, 4.69 In Height, White, +32 °F Operating Temperature, +104 °F Operating Temperature, 1 Yr Warranty, 0.26 LB/Ea |
| Weight per unit | 0.2600 (lbs/each) |
| Product Category | Lighting Dimmers |

Features

| | |
|-----------------|---------------|
| actuator | Paddle Switch |
| amperage rating | 8 |
| connection | Wire Leads |
| Connection Type | Wire Leads |
| insulation | Plastic |
| Material | Plastic/Metal |
| media | Yes |
| Poles | 1 |
| Wattage | 2216 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Gloss |
|--------|-------|

Dimensions and Weight

| | |
|------|----------------------|
| Size | 4.69 x 2.94;119 x 75 |
|------|----------------------|

Descriptions

| | |
|------------------------|--|
| Description | DIVA DV 8A 0-10V 3WAY WHITE |
| extra long description | LUT DVSTV-WH DIVA 0-10 W/SWITCHING |
| Special Features | Controls 0-10 V LED or fluorescent fixture loads, 50 mA max control current. Paddle turns on/off. Slide up to brighten, down to dim. |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00784276099622 |
| UPC | 784276099622 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Residential dimmers, motion sensors, controls, & photo cells |
| Type | Dimmer, 3-way/single-pole |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 0.26 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Lighting Control |
| Enclosure | Plastic |
| environmental conditions | Indoor use only |
| Mounting | WALLBOX |
| Operating Temperature | 32 to 104 |
| standard | UL, CSA |