



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E50SN E50 Switch Body

*Eaton Corp*

|                  |   |
|------------------|---|
| Catalog Number   | E50SN   |
| Manufacturer     | Eaton Corp  |
| Description      | Limit Switch Body, E50 Series, 1NO-1NC Contact Configuration, 10 A (Maximum Ac);1 A (Maximum DC), 240 V Ac;250 V DC, Die Cast Zinc (Enclosure) Housing Material, -14 to +201 °F, 3.14 In Overall Length, 1.54 In Overall Width, 1.73 In Overall Depth, 0.4100 LB/Ea |
| Weight per unit  | 0.4100 (lbs/each)   |
| Product Category | Limit Switch Bodies   |

### Features

|            |                                   |
|------------|-----------------------------------|
| dimensions | 3.1400 IN X 1.5400 IN X 1.7300 IN |
| Material   | Die Cast Zinc                     |

### Dimensions and Weight

|        |      |
|--------|------|
| Depth  | 1.54 |
| Height | 1.73 |
| Width  | 1.54 |

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | E50 SWITCH BODY                     |
| extra long description | ETN E50SN E50 LS SWITCH BODY,NEUTRA |

### Manufacturer Information

|       |                     |
|-------|---------------------|
| Brand | EATON CUTLER-HAMMER |
| GTIN  | 00782113308807      |
| UPC   | 782113308807        |

### Taxonomies, Classifications, and Categories

|                      |                                 |
|----------------------|---------------------------------|
| Category Description | LIMIT SWITCHES                  |
| Type                 | Heavy duty plug-in limit switch |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 0.41 |

### Uses, Certifications, and Standards

|                                |   |
|--------------------------------|---|
| Application                    | Water and Wastewater Systems - Water and Wastewater Systems - OtherStationary Mach Equip In Factory - Machine Tools: CuttingStationary Mach Equip In Factory - Machine Tools: FormingInd Facilities & Factories - Industrial Facilities/Factories - Other |
| Operating Temperature standard | 14<br>UL Listed,CSA Certified,RoHS Compliant,CE Marked  |