



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## E55CAL12T111E 12MM STD Ind Prox Plastic 3W DC PNP

*Eaton Corp*

Catalog Number	E55CAL12T111E
Manufacturer	Eaton Corp
Description	Tubular Inductive Proximity Sensor, E55, 4 MM Range, Straight, 12 MM, Unshielded, Output On, 3-Wire, 6.6 FT, 200 Ma, PVC, Nonmetallic, No PNP Open Collector, 10-30 VDC
Weight per unit	0.5000 (lbs/each)
Product Category	Inductive Proximity Sensor

### Features

dimensions	2.1700 IN X 0.4700 IN X 0.4700 IN
------------	-----------------------------------

### Descriptions

Description	12MM STD IND PROX PLASTIC 3W DC PNP
extra long description	ETN E55CAL12T111E 12MM STD IND PROX
Features	55 series photoelectric sensors are identical to the 50 series except without the interchangeable outputs or logic functions. They offer durability and high optical performance in a cost-effective, self-contained package. The 55 Series features sensors with AC and DC operation in a single unit. A relay option is available on these models that provides a 3 Amp SPDT relay output for high current switching.
Long Description	Tubular Inductive Proximity Sensor, E55, 4 mm range, Straight, 12 mm, Unshielded, Output ON, 3-wire, 6.6 ft, 200 mA, PVC, Nonmetallic, NO PNP open collector, 10-30 Vdc
Product Type	12MM STD Ind Prox Plastic 3W DC PNP

### Manufacturer Information

Brand	Eaton
GTIN	00782113888187
Manufacturers Part Number	E55CAL12T111E
UPC	782113888187

### Taxonomies, Classifications, and Categories

Category Description	SENSORS
Type	Photoelectric Sensor

### Packaging

Carton	1
Weight Per each	0.5



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application	Stationary Machinery and Equipment Outside Factory - Car Wash
environmental conditions	NEMA 3, NEMA 3S, NEMA 4, NEMA 4X, NEMA 13, IP66
standard	CE,RoHS Compliant,CE Marked