



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ECN5422AAER63D Pump Panel - 60A Fusible SW Nema 3R SZ 2 120VAC CO *Eaton Corp*

Catalog Number	ECN5422AAER63D
Manufacturer	Eaton Corp
Description	Eaton Freedom Industrial Pump Panel, Fusible Disconnect, Nema 3R Painted Steel Enclosure, 120V/60 HZ, 110V/50 HZ Coil, 60A/600V Type R Fuse Clip, 9-45A Solid-State Electronic Overload Relay, Nema Size 2 Frame
Weight per unit	75.0 (lbs/each)
Product Category	Reversing Starters With Circui

### Features

Coil Voltage	120V/60 Hz, 110V/50 Hz
--------------	------------------------

### Dimensions and Weight

Depth	40
Height	12
Width	20

### Descriptions

Description	PUMP PANEL - 60A FUSIBLE SW NEMA 3R SZ 2 120VAC CO
extra long description	ETN ECN5422AAE-R63/D PP 60A FUS SW
Features	Eaton's industrial pump panels are combination starters that are designed for irrigation, oil well, gas and other pump applications. The enclosure is NEMA Type 3R to provide weather-tight protection and is available in several sizes, depending on the customer's control option requirements. The disconnect, contactor and overload relay are the same as used in Freedom lines of combination starters.
Long Description	Eaton Freedom Industrial Pump Panel, Fusible disconnect, NEMA 3R Painted steel enclosure, 120V/60 Hz, 110V/50 Hz coil, 60A/600V Type R fuse clip, 9-45A solid-state electronic overload relay, NEMA size 2 frame
Product Type	PP 60A Fus SW N3R SZ2 120V CL

### Manufacturer Information

Brand	Eaton
GTIN	00786685455273
Manufacturers Part Number	ECN5422AAE-R63/D
UPC	786685455273

### Taxonomies, Classifications, and Categories

Category Description	PUMP PANELS
----------------------	-------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	75

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other Stationary Machinery and Equipment Outside Factory - Pumps and Compressors
standard	UL Listed, OSHPD Certified, cUL Listed, ABS Certified