

# Eaton ECN5522CAF-C1R63/D

Catalog Number: ECN5522CAF-C1R63/D

Eaton Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R painted steel enclosure, NEMA size 2, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 9-45A solid-state relay w/o ground fault, 50A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Industrial pump panel	ECN5522CAF-C1R63/D
<b>UPC</b>	<b>Product Length/Depth</b>
786685456157	8.47 in
<b>Product Height</b>	<b>Product Width</b>
12 in	18.86 in
<b>Product Weight</b>	<b>Warranty</b>
75 lb	1 year

## Certifications

OSHDP Certified  
cUL Listed  
UL Listed

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

50A

Overload relay

9-45A solid-state relay without ground fault

Size

NEMA size 2

Special features

Wired for 480V

System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5522CAF-C1R63/D](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton ECN5522CAF-C1R63/D

Catalog Number: ECN5522CAF-C1R63/D

Eaton Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R painted steel enclosure, NEMA size 2, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 9-45A solid-state relay w/o ground fault, 50A



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Industrial pump panel	ECN5522CAF-C1R63/D
<b>UPC</b>	<b>Product Length/Depth</b>
786685456157	8.47 in
<b>Product Height</b>	<b>Product Width</b>
12 in	18.86 in
<b>Product Weight</b>	<b>Warranty</b>
75 lb	1 year

## Certifications

OSHDP Certified  
cUL Listed  
UL Listed

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

50A

Overload relay

9-45A solid-state relay without ground fault

Size

NEMA size 2

Special features

Wired for 480V

System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5522CAF-C1R63/D](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)