



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Freedom Industrial Pump Panel

ECN5422CAE-P6R63/D

UPC:786685455310

### Dimensions:

- **Height:** 12 IN
- **Length:** 40 IN
- **Width:** 20 IN

**Weight:**75 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 460V/60 Hz, 440V/50 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Actuator:** Pushbutton omitted
- **Disconnect:** Fusible
- **Frame Size:** NEMA size 2
- **Fuse Clip Rating:** 60A/600V
- **Fuse Clip Type:** Type R
- **Overload Relay:** 9-45A solid-state electronic overload relay

### Supporting documents:

- [Eatons Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN5422CAE-P6R63/D](#)

### Certifications:

- OSHPD Certified
- ABS Certified
- UL Listed
- cUL Listed

**Product compliance:** No Data







Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Freedom Industrial Pump Panel

ECN5422CAE-P6R63/D

UPC:786685455310

### Dimensions:

- **Height:** 12 IN
- **Length:** 40 IN
- **Width:** 20 IN

**Weight:**75 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Coil Voltage:** 460V/60 Hz, 440V/50 Hz
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted steel
- **Actuator:** Pushbutton omitted
- **Disconnect:** Fusible
- **Frame Size:** NEMA size 2
- **Fuse Clip Rating:** 60A/600V
- **Fuse Clip Type:** Type R
- **Overload Relay:** 9-45A solid-state electronic overload relay

### Supporting documents:

- [Eaton's Volume 10-Enclosed Control](#)
- [Eaton Specification Sheet - ECN5422CAE-P6R63/D](#)

### Certifications:

- OSHPD Certified
- ABS Certified
- UL Listed
- cUL Listed

**Product compliance:** No Data



