

Eaton ECN5512CAE-C1R63/C

Catalog Number: ECN5512CAE-C1R63/C

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R steel enclosure, NEMA size 1, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 4-20A solid-state relay without ground fault, 30A breaker



General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5512CAE-C1R63/C
UPC	Product Length/Depth
786685547183	8.47 in
Product Height	Product Width
38.4 in	18.86 in
Product Weight	Warranty
75 lb	1 year

Certifications

UL Listed
cUL Listed
OSHDP Certified

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

30A

Overload relay

4-20A solid-state relay without ground fault

Size

NEMA size 1

Special features

Wired for 480V

System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5512CAE-C1R63/C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton ECN5512CAE-C1R63/C

Catalog Number: ECN5512CAE-C1R63/C

Eaton Freedom Industrial Pump Panel, Circuit breaker disconnect, Wired for 480V, NEMA 3R steel enclosure, NEMA size 1, 220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary, 4-20A solid-state relay without ground fault, 30A breaker



General specifications

Product Name	Catalog Number
Eaton Industrial pump panel	ECN5512CAE-C1R63/C
UPC	Product Length/Depth
786685547183	8.47 in
Product Height	Product Width
38.4 in	18.86 in
Product Weight	Warranty
75 lb	1 year

Certifications

UL Listed
cUL Listed
OSHDP Certified

Enclosure

NEMA 3R

Enclosure material

Painted steel

Type

Circuit breaker disconnect

Circuit breaker rating

30A

Overload relay

4-20A solid-state relay without ground fault

Size

NEMA size 1

Special features

Wired for 480V

System voltage

220/440V-240/480V primary, 110V/50 Hz-120V/60 Hz secondary

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Specifications and datasheets

[Eaton Specification Sheet - ECN5512CAE-C1R63/C](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)