



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EGE3040FFG E 3P 40A 25KA @ 415 & 480V Fixed Thermal Fixed Mag

Eaton Corp

Catalog Number	EGE3040FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 40 A, 600Y/347 Vac, 35 Kaic At 240 Vac, 25 Kaic At 480 Vac, 18 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ
Weight per unit	3.0 (lbs/each)
Product Category	3 Pole

Features

Current Rating	40 A
dimensions	2.9900 IN X 3.0000 IN X 5.5000 IN
frame	EG
interrupt rating	25 kAIC at 480 Vac18 kAIC at 600Y/347 Vac35 kAIC at 240 Vac
media	Yes
Poles	3
Trip Type	Fixed thermal, fixed magnetic
Voltage Rating	600Y/347 Vac

Descriptions

Description	E 3P 40A 25KA @ 415 & 480V FIXED THERMAL FIXED MAG
extra long description	ETN EGE3040FFG E 3P 40A 25kA 415&48
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 40 A, 600Y/347 Vac, 35 kAIC at 240 Vac, 25 kAIC at 480 Vac, 18 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz
Product Type	E 3P 40A 25KA 415&480V FXD Therm FXD Mag



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114876749
Manufacturers Part Number	EGE3040FFG
UPC	782114876749

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker

Packaging

Carton	1
Weight Per each	3

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and OEMs - Other
Frequency Rating	50/60 Hz
standard	IEC Rated,UL Listed,CSA Certified,CE Marked