



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGE3100FFG E 3P 100A 25KA @ 415 & 480V Fixed Thermal Fixed Ma Eaton Corp

|                  |   |
|------------------|---|
| Catalog Number   | EGE3100FFG  |
| Manufacturer     | Eaton Corp  |
| Description      | Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 100 A, 600Y/347 Vac, 35 Kaic At 240 Vac, 25 Kaic At 480 Vac, 18 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ |
| Weight per unit  | 2.9 (lbs/each)  |
| Product Category | 3 Pole  |

### Features

|                |                                   |
|----------------|-----------------------------------|
| Current Rating | 100 A                             |
| dimensions     | 2.9900 IN X 3.0000 IN X 5.5000 IN |
| frame          | EG                                |
| media          | Yes                               |
| Poles          | 3                                 |
| Voltage Rating | 600Y/347 Vac                      |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | E 3P 100A 25KA @ 415 & 480V FIXED THERMAL FIXED MA  |
| extra long description | ETN EGE3100FFG E 3P 100A 25KA 415&4   |
| Features               | The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren |
| Long Description       | Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 100 A, 600Y/347 Vac, 35 kAIC at 240 Vac, 25 kAIC at 480 Vac, 18 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz   |
| Product Type           | E 3P 100A 25KA 415&480V FXD Therm & Mag   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782114876824 |
| Manufacturers Part Number | EGE3100FFG     |
| UPC                       | 782114876824   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

|                      |                             |
|----------------------|-----------------------------|
| Category Description | MOLDED CASE BREAKERS        |
| Type                 | Molded case circuit breaker |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Weight Per each | 2.91 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies and<br>EOEMs - Other |
| standard    | IEC Rated,CSA Certified,UL Listed,CE Marked                                |