



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EGH3060FFG E 3P 60A 70KA @ 415 65KA @ 480V Fixed Thermal Fixe *Eaton Corp*

Catalog Number	EGH3060FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Molded Case Circuit Breaker, Eg-Frame, Eg, Fixed Thermal, Fixed Magnetic Trip, Three-Pole, 60 A, 600Y/347 Vac, 100 Kaic At 240 Vac, 65 Kaic At 480 Vac, 35 Kaic At 600Y/347 Vac, Line and Load, 50/60 HZ
Weight per unit	3.0 (lbs/each)
Product Category	3 Pole

### Features

Current Rating	60 A
dimensions	2.9900 IN X 3.0000 IN X 5.5000 IN
frame	EG
media	Yes
Poles	3
Voltage Rating	600Y/347 Vac

### Descriptions

Description	E 3P 60A 70KA @ 415 65KA @ 480V FIXED THERMAL FIXE
extra long description	ETN EGH3060FFG E 3P 60A 70kA 415 65
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G molded case circuit breaker, EG-frame, EG, Fixed thermal, Fixed magnetic trip, Three-pole, 60 A, 600Y/347 Vac, 100 kAIC at 240 Vac, 65 kAIC at 480 Vac, 35 kAIC at 600Y/347 Vac, Line and load, 50/60 Hz
Product Type	E 3P 60A 70KA 415 65KA 480V FXD TM

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114877579
Manufacturers Part Number	EGH3060FFG
UPC	782114877579



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Molded case circuit breaker

## Packaging

Carton	1
Weight Per each	3

## Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	IEC Rated, CSA Certified, UL Listed, CE Marked