



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EJWT 120/240V Percentage Timer N4X Adjustable

Nsi Industries

Catalog Number	EJWT
Manufacturer	Nsi Industries
Description	The Tork Ejwt 24-Hour Percentage Timer Switch Is Designed For A Wide Range Of Applications In The Agriculture, Industrial, Pumping or Livestock Industries. Automate Your Home or Facility to Save Energy and Money Using The Two Control Dials, One Of Which Sets The Cycle Time and The Second Of Which Sets The Percentage Of Time That The Timer Will Be On. Featuring A Total Of 960 Different Time Combinations, This Timer Matches The Needs Of Most Industrial Applications and Meets Nema-4X Standards For Water Resis
Weight per unit	1.6 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	SPDT
Base	Screw
Contact Rating	120-240 VAC
Phase	Single Phase
Poles	1
Timing Range	0 to 100 Percent

Dimensions and Weight

Size	L=4.812 - H=4.812 - W=3.312
------	-----------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	120/240V PERCENTAGE TIMER N4X ADJUSTABLE
extra long description	TORK EJWT 24 Hr Max Percentage Time
Features	The EJWT percentage timer provides a simple solution for controlling appliances or equipment that run on a regularly repeating schedule. Simply adjust the two dials to control the cycle time and percentage on, selecting from 960 time combinations to match your needs. Key applications include feeding livestock or poultry, well or oil pumping, ventilation, greenhouses, or a wide range of agricultural or livestock needs. This switch saves you time and effort by automating your application no matter the time i
Long Description	The TORK EJWT 24-Hour Percentage Timer Switch is designed for a wide range of applications in the agriculture, industrial, pumping or livestock industries. Automate your home or facility to save energy and money using the two control dials, one of which sets the cycle time and the second of which sets the percentage of time that the timer will be on. Featuring a total of 960 different time combinations, this timer matches the needs of most industrial applications and meets NEMA-4X standards for water resis
Product Type	24 HR Max Percentage Timer
Special Features	SPDT Percentage Timer - 960 Time Combinations With Two Dials

Manufacturer Information

Brand	NSi
GTIN	00786261825131
Manufacturers Part Number	EJWT
UPC	786261825131

Taxonomies, Classifications, and Categories

Category Description	TIMERS
Type	Percentage Timer

Packaging

Carton	1
Weight Per each	1.56



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	NSI
Enclosure	NEMA 4X Indoor
environmental conditions	32 to + 122 F
Frequency Rating	60 Hz
Mounting	Screw Mount
Operating Temperature	32 to + 122 F
standard	UL-CSA