



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EMRGLED5500ACDF 5W 120-277V Led Emergency Backup Dual Flex Cable *Keystone Technologies*

Catalog Number	EMRGLED5500ACDF
Manufacturer	Keystone Technologies
Description	Led Emergency Backup, 5W - 500 Lumen Constant Power Design. 120-277V Input. Dual Flex Cable Design. Installs On Primary Side Of Ac Powered Led Load. Optimized For Type B Compact Lamps and Led Downlight Fixtures. Includes Instruction Sheets & Test Switch
Weight per unit	2.0 (lbs/each)
Product Category	Led Emergency Drivers

Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	500
Nominal Length	N/A
Nominal Size	N/A
Number of Lamps	N/A
Output Current	Load Dependant
Output Voltage	40-100
Sensor Type	N/A
Wattage	5
Wire Type	Dual Flex Conduit

Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	N/A
color temperature	N/A
housing color	N/A

Descriptions

Construction	ONE PIECE
Description	5W 120-277V LED EMERGENCY BACKUP DUAL FLEX CABLE
extra long description	Key KT-EMRG-LED-5-500-AC /DF-IP 25W
Long Description	LED Emergency Backup, 5W - 500 Lumen Constant Power Design. 120-277V Input. Dual Flex Cable Design. Installs on Primary Side of AC Powered LED load. Optimized for Type B Compact Lamps and LED downlight fixtures. Includes Instruction Sheets & Test Switch
Product Type	25W, 7" Round Ac Led Light Engine Kit, Phase Dimming, 3000,



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Keystone
GTIN	00843654120843
Manufacturers Part Number	KT-EMRG-LED-5-500-AC /DF-IP
UPC	843654120843

Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
----------------------	--------------------

Packaging

Carton	1
Package	10
Weight Per each	2

Uses, Certifications, and Standards

Energy Star	N
-------------	---