

---

## 30" PLASTIC ENCLOSURE WITHOUT HINGED DOOR (PACK OF 5)

ENP3080-5 | [On-Q](#)



---

### FEATURES & BENEFITS

Constructed with a robust, wireless transparent ABS plastic material, this lightweight enclosure is designed to integrate wireless devices into traditional structured wiring installations. The enclosure mounts easily for both surface and recessed applications.

Hinged cover (ENP3060) purchased separately to complete installation during trim-out phase. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Universal mounting grid maximizes compatibility with 3rd party products without additional brackets.
- Installs into a single stud bay and has staggered mounting tabs to allow multiple enclosures to mount in adjacent stud bays.
- Tapered design allows enclosures to stack for efficient transportation and warehousing.
- Top surface includes five 2" knockouts; rubber grommets available for purchase ([AC1034](#)).
- Bottom surface includes two AC receptacle box knockouts and two knockouts allowing vertical stackability.
- Compatible for both surface or recessed mounting applications
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 104 mm

Depth (US): 4.09"

Height (Metric): 782 mm

Height (US): 30.08"

Width (Metric): 434mm

Width (US): 17.1"

Product Weight (Metric): 12.5 kg

Product Weight (US): 27.5 lbs

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C

---

## 30" PLASTIC ENCLOSURE WITHOUT HINGED DOOR (PACK OF 5)

ENP3080-5 | [On-Q](#)



---

### FEATURES & BENEFITS

Constructed with a robust, wireless transparent ABS plastic material, this lightweight enclosure is designed to integrate wireless devices into traditional structured wiring installations. The enclosure mounts easily for both surface and recessed applications.

Hinged cover (ENP3060) purchased separately to complete installation during trim-out phase. [Click here](#) to learn more about the unique features that will save you time and simplify installation.



- Made with ABS plastic, the enclosure is designed to integrate wireless devices without interference.
- Universal mounting grid maximizes compatibility with 3rd party products without additional brackets.
- Installs into a single stud bay and has staggered mounting tabs to allow multiple enclosures to mount in adjacent stud bays.
- Tapered design allows enclosures to stack for efficient transportation and warehousing.
- Top surface includes five 2" knockouts; rubber grommets available for purchase ([AC1034](#)).
- Bottom surface includes two AC receptacle box knockouts and two knockouts allowing vertical stackability.
- Compatible for both surface or recessed mounting applications
- UL listed.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: White (Paintable)\*

Type: Enclosure

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: UL 60950-1 & CAN/CSA C22.2 No. 60950-01-07 Information Technology Equipment, Including Electrical Business Equipment

CSA Standard: Yes

UL Listing No: UL 2416, Audio/Video, Information and Communication Technology Equipment Cabinet, Enclosure and Rack Systems UL 985, Household Fire-Warning System Units ULC-S545, Residential Fire Warning System Control Units UL 1023, Household Burglar-Alarm System Units ULC/ORD-C1023, Household Burglar Alarm System Units  
UL Standard: Yes

## **CONSTRUCTION INFORMATION**

Material 1: ABS Plastic

## **DIMENSIONS**

Depth (Metric): 104 mm

Depth (US): 4.09"

Height (Metric): 782 mm

Height (US): 30.08"

Width (Metric): 434mm

Width (US): 17.1"

Product Weight (Metric): 12.5 kg

Product Weight (US): 27.5 lbs

## **TECHNICAL INFORMATION**

Material: ABS Plastic

Operating Temperature (Celsius): 0°C to 50°C