

DESCRIPTION

White reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Socket supporting trim, available in high gloss appliance white with white reflector. TS version uses torsion springs to hold trim tight to ceiling.

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

Lamp Listings - Incandescent

ET700	85W BR30, 120W BR40, 100W R30, 75W PAR30L, 100W A19
ET700R	65W BR30, 75W PAR30L

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 75W R30, 90W BR40
EI700AT	
EI700ATNB	
EI700NB	
EI700R	
EI700RAT	


EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	




ERT712
Gloss White Trim,
White Reflector



ERT712TS
Gloss White Trim, White
Reflector and Torsion Spring




ERT712
Height: 5-3/8" [136mm]
Outside Diameter: 7-1/4" [184mm]



ERT712TS
Height: 5-3/8" [136mm]
Outside Diameter: 7-1/4" [184mm]

ORDERING INFORMATION

Trim



ERT712 = 6" High gloss appliance white trim with white reflector
ERT712TS = 6" High gloss appliance white trim with white reflector, torsion spring

DESCRIPTION

White reflector trim in the 6" All-Pro trim family for use in Halo and All-Pro recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

Socket supporting trim, available in high gloss appliance white with white reflector. TS version uses torsion springs to hold trim tight to ceiling.

Lamp Listings - GU24

H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

Lamp Listings - Incandescent

ET700	85W BR30, 120W BR40, 100W R30, 75W PAR30L, 100W A19
ET700R	65W BR30, 75W PAR30L

EI700	40W A19, 65W BR30, 75W PAR30, 75W PAR30L, 75W R30, 90W BR40
EI700AT	
EI700ATNB	
EI700NB	
EI700R	
EI700RAT	


EI700U	60W A19, 75W PAR30, 75W PAR30L, 85W BR30, 100W R30, 120W BR40
EI700UAT	




ERT712
Gloss White Trim, White Reflector



ERT712TS
Gloss White Trim, White Reflector and Torsion Spring



ERT712
Height: 5-3/8" [136mm]
Outside Diameter: 7-1/4" [184mm]




ERT712TS
Height: 5-3/8" [136mm]
Outside Diameter: 7-1/4" [184mm]

ERT712

6-Inch White Reflector

ORDERING INFORMATION

Trim



ERT712 = 6" High gloss appliance white trim with white reflector
ERT712TS = 6" High gloss appliance white trim with white reflector, torsion spring