



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESX1LEDP450KR3MV ESX1 Led P4 50K R3 Mvolt Upa BLS DDBXD M2 *Lithonia Lighting*

| | |
|------------------|---|
| Catalog Number | ESX1LEDP450KR3MV |
| Manufacturer | Lithonia Lighting |
| Description | The Lithonia Lighting Esx Led Area Luminaire Provides The Combination Of Best Product Value, Best Price and Best Delivery. Esx Is Ideal For One-For-One Replacement Of Hid Area Lighting and Provides Up to 76% Energy Savings, Long Service Life and Fast Payback. All Esx Luminaires Feature Adjustable Light Output, Providing Two Light Levels From One Product, Allowing Greater Flexibility While Helping Reduce Inventory Costs. The Luminaires Also Feature A Reversible Arm That Allows For Mounting On Both Round and |
| Weight per unit | 11.7 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|---|
| average life | 60,000 |
| dimensions | 19.94 x 12 x 2.87 |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 21,000 LM,22,000 LM,23,000 LM,24,000 LM,25,000 LM |
| Material | Aluminum |
| Maximum Operating Temperature | 40 |
| media | Yes |
| Power Source | Hardwired |
| Shape | Rectangular |
| Voltage Rating | 120-277 |
| Wattage | 200 |

Material, Color, and Finish

| | |
|-----------------------------|--------------|
| Color | Bronze |
| color rendering index (cri) | 70 |
| color temperature | 5000 |
| Finish | Gloss |
| fixture material | aluminum |
| Lens Color | Clear |
| Lens Material | Glass |
| Style | CONTEMPORARY |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Dimensions and Weight

| | |
|--------|------------------|
| Height | 2.87 |
| Length | 19.94 |
| Size | 19.94x12x2.87 IN |
| Width | 12 |

Descriptions

| | |
|------------------------|---|
| Description | ESX1 LED P4 50K R3 MVOLT UPA BLS DDBXD M2 |
| extra long description | LITH ESX1 LED P4 50K R3 MVOLT UPA B |
| Features | Design Select |
| Long Description | The Lithonia Lighting ESX LED area luminaire provides the combination of best product value, best price and best delivery. ESX is ideal for one-for-one replacement of HID area lighting and provides up to 76% energy savings, long service life and fast payback. All ESX luminaires feature adjustable light output, providing two light levels from one product, allowing greater flexibility while helping reduce inventory costs. The luminaires also feature a reversible arm that allows for mounting on both round and |
| Product Type | Area Light |

Manufacturer Information

| | |
|---------------------------|--------------------------------|
| Brand | Lithonia Lighting |
| GTIN | 00194994838531 |
| Manufacturers Part Number | ESX1 LED P4 50K R3 MVOLT UPA B |
| UPC | 194994838531 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED CANOPY, PARKING, POLE MOUNTED & ROADWAY LIGHTING |
| Type | AREA LIGHT |

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Weight | 11.24 |
| Weight Per each | 11.73 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Automotive & Parking, Offices & Banks, Retail |
| environmental conditions | OUTDOOR |
| Mounting | Arm Mount, Surface |
| standard | C-UL-USDLC Premium, Nighttime Friendly |