



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESXF5AL0SWW2XV0L ESXF5 Alo SWW2 Xvolt Ys DDB 277-480V

Lithonia Lighting - Acuity

| | |
|------------------|---|
| Catalog Number | ESXF5AL0SWW2XV0L |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The Lithonia Lighting® ESXF5 Led All-In-One Floodlight Gives You The Superior Illumination You Want. ESXF5 Delivers Easy Access to Adjustable Lumen Output, Color Switching, and A Selectable Photocell, So You Always Have The Luminaire You Need On The Spot. Choose Your Mounting With Two Popular Mounting Options Standard In Each Box; Yoke or Slipfitter. ESXF5 Is A True Replacement For 1000W Hid Luminaires and Delivers Up to 50,000 Lumens. |
| Weight per unit | 19.0 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|-------------------------------|-------------------------------|
| average life | 36,000 |
| dimnable | Yes |
| Hardware | Yes |
| Lamp Included | Yes |
| Lamp Type | LED - Static |
| lumens | 30,000 LM,40,000 LM,50,000 LM |
| Material | Aluminum |
| Maximum Operating Temperature | 25 |
| Shape | Rectangular |
| Voltage Rating | 277-480 |

Material, Color, and Finish

| | |
|-----------------------------|------------------|
| Color | Bronze |
| color rendering index (cri) | 80 |
| color temperature | 3000 ,4000 ,5000 |
| Finish | Gloss |

Dimensions and Weight

| | |
|--------|------|
| Height | 3.5 |
| Length | 24.5 |
| Width | 16 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | ESXF5 ALO SWW2 XVOLT YS DDB 277-480V |
| extra long description | LITH ESXF5 ALO SWW2 XVOLT YS DDB ES |
| Long Description | The Lithonia Lighting® ESXF5 LED all-in-one floodlight gives you the superior illumination you want. ESXF5 delivers easy access to adjustable lumen output, color switching, and a selectable photocell, so you always have the luminaire you need on the spot. Choose your mounting with two popular mounting options standard in each box; yoke or slipfitter. ESXF5 is a true replacement for 1000W HID luminaires and delivers up to 50,000 lumens. |
| Product Type | Floodlight |

Manufacturer Information

| | |
|---------------------------|-----------------------------|
| Brand | Lithonia Lighting |
| GTIN | 00197589243734 |
| Manufacturers Part Number | ESXF5 ALO SWW2 XVOLT YS DDB |
| UPC | 197589243734 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |
|----------------------|---|

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 19 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Automotive & Parking,Decorative,Education,Entertainment,Food Service,Government,Healthcare,Hospitality,House of Worship,Manufacturing,Offices & Banks,Parking Garage,Residential,Retail |
| environmental conditions | OUTDOOR |
| Mounting | Tenon Slipfitter,Yoke |
| standard | C-UL-US DLC Standard |