



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EU2LM12 Led Emergency Light Low Profile White

Lithonia Lighting - Acuity

| | |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | EU2LM12 |
| Manufacturer | Lithonia Lighting - Acuity |
| Description | The Lithonia Lighting EU2L Led Emergency Light Is Suitable For Emergency Lighting Applications Such As Stairways and Hallways. Designed With All-Inclusive Lamp, Reflector and Lens Assembly. Its Low Profile and Dual Lamp Heads Make The EU2L Ideal For Safely Illuminating The Path Of Egress In Small Spaces At Lower Mounting Heights. It Can Be Wall or Ceiling Mounted and Will Provide 90 Minutes Of Emergency Power In The Case Of Power Loss. |
| Weight per unit | 0.8000 (lbs/each) |
| Product Category | Emergency Lighting |

Features

| | |
|-------------------------------|-------------------------|
| dimensions | 7.875x2.75x4.5 |
| Fixture Type | Emergency Lighting Unit |
| Lamp Type | LED - Static |
| lumens | 150 LM |
| Maximum Operating Temperature | 40 |
| pallet quantity | 756 |
| Power Source | Hardwired |
| Voltage Rating | 120/277 |
| Warranty | 2 |
| Wattage | 0.75 |

Material, Color, and Finish

| | |
|-------------------|---------|
| Color | White |
| color temperature | 5000 |
| Lens Color | Clear |
| Lens Material | Plastic |

Dimensions and Weight

| | |
|--------|-------|
| Height | 4.5 |
| Length | 7.875 |
| Width | 2.75 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | LED EMERGENCY LIGHT LOW PROFILE WHITE |
| extra long description | LITH EU2L M12 Lithonia Lighting LED |
| Features | Contractor Select |
| Long Description | The Lithonia Lighting EU2L LED Emergency Light is suitable for emergency lighting applications such as stairways and hallways. Designed with all-inclusive lamp, reflector and lens assembly. Its low profile and dual lamp heads make the EU2L ideal for safely illuminating the path of egress in small spaces at lower mounting heights. It can be wall or ceiling mounted and will provide 90 minutes of emergency power in the case of power loss. |
| Product Type | Emergency Lighting Unit |

Manufacturer Information

| | |
|---------------------------|-------------------|
| Brand | Lithonia Lighting |
| GTIN | 00191848035351 |
| Manufacturers Part Number | EU2L M12 |
| UPC | 191848035351 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | Emergency & Exit Lighting |
| Type | Emergency Lighting Unit |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 12 |
| Weight | 0.7 |
| Weight Per each | 0.8 |

Uses, Certifications, and Standards

| | |
|--------------------------|----------------------------------------------|
| Application | Education,Hospitality,Offices & Banks,Retail |
| environmental conditions | Indoor |
| Mounting | SURFACE |
| standard | NFPA 101,ULCA Title 20 |