



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1550 Wilson Rd.
77338-0000, TX Humble
Phone: 281-548-0169
Fax: 281-548-0198



EW103B Multivolt 7 Day Supercap Indoor/Outdoor 1 CH. 40a

Nsi Industries

| | |
|------------------|--------------------------|
| Catalog Number | EW103B |
| Manufacturer | Nsi Industries |
| Description | Digital Timer DPST |
| Weight per unit | 1.7 (lbs/each) |
| Product Category | Electronic Time Switches |

Features

| | |
|----------------|--------------|
| action | DPST |
| Base | Screw |
| Contact Rating | 120-277 VAC |
| Phase | Single Phase |
| Poles | 2 |
| Timing Range | 7 DAY |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=5.062 - H=8.312 - W=3.062 |
|------|-----------------------------|

Descriptions

| | |
|------------------------|--|
| Description | MULTIVOLT 7 DAY SUPERCAP INDOOR/OUTDOOR 1 CH. 40A |
| extra long description | TORK EW103B 7 Day Digital Timer One |
| Features | Tork 7 Day 1 Channel DPST Digital Time Switch APPLICATIONS: Outdoor Signs Heating and Air Conditioning Lighting Security FEATURES: INPUT SUPPLY: 120-277 VAC 50/60Hz INPUT VOLTAGE: 120-277 VAC 50/60Hz OUTPUT DRY CONTACTS: DPST POWER CONSUMPTION: 6VA Max. TIMING ACCURACY: Line Frequency SCHEDULING: 20 ON/OFF set points repeat each day. Minimum Setting 1 minute. NO. OF CHANNELS: 1 Channel DAYLIGHT SAVINGS: Automatic adjustment (can be omitted) LEAP YEAR: Automatic Compensation MANUAL OVERRIDE: Until the next |
| Long Description | Digital Timer DPST |
| Product Type | 7 Day Digital Timer One Channel 30A 120-277V DPST Indoor/Out |
| Special Features | 20 On-Off Set Points - Daylight Savings Auto - Leap Year Automatic Compensation |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | TORK |
| GTIN | 00786261824417 |
| Manufacturers Part Number | EW103B |
| UPC | 786261824417 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1550 Wilson Rd.
77338-0000, TX Humble
Phone: 281-548-0169
Fax: 281-548-0198

Taxonomies, Classifications, and Categories

Category Description 1PH MANUAL STARTERS

Type 7 Day Time Switch - 1 Or 2 Channel

Packaging

Carton 1

Weight Per each 1.7

Uses, Certifications, and Standards

Application NSI

Enclosure NEMA 3R Plastic Indoor-Outdoor

environmental conditions -40 to + 149 F

Frequency Rating 50-60 Hz

Mounting Screw Mount

Operating Temperature -40 to + 149 F

standard UL917