



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EYS29 Elbow Seal 3/4 Verticle *Crouse-Hinds*

Catalog Number	EYS29
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Eys Conduit Sealing Fitting, Feraloy Iron Alloy and/or Ductile Iron, Vertical Only, 3/4", Elbow Seal
Weight per unit	1.5 (lbs/each)
Product Category	Sealing Bodies

Features

connection	Female Threaded, Female Threaded
dimensions	3.4700 IN X 1.7500 IN X 3.6900 IN

Material, Color, and Finish

Finish	Electrogalvanized With Aluminum Acrylic Painted
--------	---

Descriptions

Description	ELBOW SEAL 3/4 VERTICLE
extra long description	CRS-H EYS29 3/4 ELBOW SEAL VERTICAL
Features	Crouse-Hinds series EYS and EZS explosionproof sealing fittings restrict the passage of gases, vapors or flames from one portion of the electrical installation to another, limit explosions to the sealed off enclosure, and limit pre-compression or "pressure piling" in conduit systems. EYS sealing fittings are available for installation in either vertical only or in both horizontal or vertical positions. They are available in a variety of materials, including Feraloy iron alloy and/or ductile iron, copper-
Long Description	Eaton Crouse-Hinds series EYS conduit sealing fitting, Feraloy iron alloy and/or ductile iron, Vertical only, 3/4", Elbow seal
Product Type	3/4 Elbow Seal Vertical Position
Special Features	Vertical Position

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274378800
Manufacturers Part Number	EYS29
UPC	782274378800

Taxonomies, Classifications, and Categories

Category Description	HAZARDOUS LOCATION FITTINGS
Type	Conduit sealing fitting

Packaging

Carton	1
Package	5
Weight Per each	1.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Enclosure	CLASS I DIV 1 2 GROUP C D, CLASS II DIV 1 2 GROUP E F G, CLASS
	III
standard	UL 886, CSA C22.2