



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F1X1.5LG6 1X1-1/2X72" LT Gry NM Slot Duct *Panduit Corporation*

Catalog Number	F1X1.5LG6
Manufacturer	Panduit Corporation
Description	The F1X1.5LG6 Panduct Lead-Free PVC Narrow Slot Wiring Duct Features A Narrow Slot/Finger Design That Closely Matches The Spacing Of High-Density Components. Upper and Lower Scorelines Allow For Easy Finger/Sidewall Section Removal. UI 94 Flame Class Of V-0 With A UI Recognized Continuous-Use Temperature Up to 122°F (50°C). Mounting Holes Provided. Lead-Free PVC. 1" X 1.5" (25.4 MM X 38.1 MM) and 6' (1.83 M) Long. Cover Sold Separately. Color Light Gray.
Weight per unit	0.1567 (lbs/each)
Product Category	Ducts, Raceways, Runways, Tray

Features

connection	Mounting Holes
Material	PVC
media	Yes

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Height	1.62
Length	6.00
Size	1.00 x 1.50
Width	1.25

Descriptions

Description	1X1-1/2X72" LT GRY NM SLOT DUCT
extra long description	PAN F1X1.5LG6 Panduct® F1X1.5LG6 Ba
Long Description	The F1X1.5LG6 Panduct Lead-Free PVC Narrow Slot Wiring Duct features a narrow slot/finger design that closely matches the spacing of high-density components. Upper and lower scorelines allow for easy finger/sidewall section removal. UL 94 flame class of V-0 with a UL recognized continuous-use temperature up to 122°F (50°C). Mounting holes provided. Lead-free PVC. 1" x 1.5" (25.4 mm x 38.1 mm) and 6' (1.83 m) long. Cover sold separately. Color Light Gray.
Product Type	Panduct® F1X1.5LG6 Base Wiring Duct



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PANDUIT
GTIN	00074983375073
Manufacturers Part Number	F1X1.5LG6
UPC	074983375073

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Base Wiring Duct

Availability

minimum qty	6
-------------	---

Packaging

Carton	120
Weight Per foot	0.1567

Uses, Certifications, and Standards

Application	Narrow slot/finger design provides more slots to fit the spacing of high-density terminal block applications
standard	CSA Approved; RoHS Compliant, UL Recognized, CE Compliant