

Eaton FD3040

Catalog Number: FD3040

Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 40 A, 600 Vac, 250 Vdc, Load side, 50/60 Hz



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	FD3040
	UPC
	786679305676
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
4.13 in	4.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

40 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

FD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Load side

Frame

F

Frequency rating

50/60 Hz

Interrupt rating

65 kAIC at 240 Vac

35 kAIC at 480 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[StrandAble terminals product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[Motor protection circuit breakers product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[FD3 2D PDF](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

[FD3 3D Model Xchange](#)

[FD3 2D Drawing Xchange](#)

[FD3 3D Inventor](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Eaton Specification Sheet - FD3040](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[F-Frame 310+ Molded-case circuit breakers 15-225A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)