

Eaton FD3175

Catalog Number: FD3175

Eaton Series C complete molded case circuit breaker, F-frame, FD, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 175 A, 600 Vac, 250 Vdc, 65 kAIC at 240 Vac, 35 kAIC at 480 Vac



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	FD3175
	UPC
	786679015384
Product Length/Depth	Product Height
3.38 in	6 in
Product Width	Product Weight
4.13 in	4.5 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

175 A

Voltage rating

600 Vac, 250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

FD

Circuit breaker frame type

Complete breaker

Series

Series C

Terminals

Line and load

Frame

F

Frequency rating

50 to 60 Hz

Interrupt rating

35 kAIC at 480 Vac

65 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Motor protection circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Breaker service centers](#)

[Counterfeit and Gray Market Awareness Guide](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[FD3 2D PDF](#)

[FD3 3D Model Xchange](#)

[FD3 2D Drawing Xchange](#)

[Time Current Curves for Series C® F-Frame Circuit Breakers](#)

[F-frame Molded Case Circuit Breaker Drawing](#)

[FD3 3D Inventor](#)

Installation instructions

[Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - FD3175](#)

[Series C F-Frame molded case circuit breakers](#)

Series C J-Frame molded case circuit breakers time current curves

F-Frame 310+ Molded-case circuit breakers 15-225A

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)