



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FDC32 2G FDC Box *Crouse-Hinds*

Catalog Number	FDC32
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet FD Device Box, Deep, Feraloy Iron Alloy, Two-Gang, C Shape, 1"
Weight per unit	4.8 (lbs/each)
Product Category	FS & FD Type Boxes & Covers

Features

Cable Entry	(1) Each End
dimensions	4.1900 IN X 2.6900 IN X 6.3100 IN
Material	Electrogalvanized With Aluminum Acrylic Painted Feraloy Iron Alloy

Dimensions and Weight

Size	1 in
------	------

Descriptions

Description	2G FDC BOX
extra long description	CRS-H FDC32 1 NPT DE CST IRON FD BX
Features	Crouse-Hinds series FS and FD device boxes are installed in non-hazardous area conduit systems to accommodate wiring devices, act as pull boxes or provide openings for taps and splices. They are suitable for use in wet locations when used with gasketed covers. FS and FD device boxes are available in two box depths with a wide variety of gang configurations, hub configurations and hub sizes. They are manufactured in cast iron, aluminum, stainless steel and malleable iron. Malleable iron boxes are also a
Long Description	Eaton Crouse-Hinds series Condulet FD device box, Deep, Feraloy iron alloy, Two-gang, C shape, 1"
Product Type	1 NPT De CST Iron FD BX Two GNG MTG Lugs
Special Features	Configuration Type FDC, With Mounting Lug, Dimension 4-5/8 In Width X 2-11/16 In Depth X 6-5/16 In Height

Manufacturer Information

Brand	Eaton
GTIN	00782274398501
Manufacturers Part Number	FDC32
UPC	782274398501

Taxonomies, Classifications, and Categories

Category Description	FS BOXES AND COVERS
Type	DEVICE BOX



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.8

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
Mounting	SURFACE
standard	UL 514, CSA C22.2, Federal Specification W-C-5860