



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **FLED100R1AUNV8CS 100W Led Flood 3K/4K/5K Select 14300LM BRZ 120/277** *Keystone Technologies*

Catalog Number	FLED100R1AUNV8CS
Manufacturer	Keystone Technologies
Description	100W Led Flood Light Feat. Color Select, Rectangular Series 1 With Built In Photocell. 120-277V Input, 3000K/4000K/5000K. Standard Bronze Housing. Wide Beam Spread, Slip Fitter Mount
Weight per unit	10.1 (lbs/each)
Product Category	Lighting

### Features

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	IP65
lumens	13400
Nominal Length	N/A
Nominal Size	Rectangular
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	Photocell only
Wattage	100
Wire Type	N/A

### Material, Color, and Finish

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	N/A
housing color	Bronze

### Descriptions

Construction	N/A
Description	100W LED FLOOD 3K/4K/5K SELECT 14300LM BRZ 120/277
extra long description	Key KT-FLED100-R1A-UNV-8CSB-VDIM 40
Long Description	100W LED Flood Light feat. Color Select, Rectangular Series 1 with built in photocell. 120-277V Input, 3000K/4000K/5000K. Standard Bronze Housing. Wide Beam Spread, Slip Fitter Mount
Product Type	400W Equiv., 100W, 13400 Lumens Built In Photocell. Univr Mo



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654129006
Manufacturers Part Number	KT-FLED100-R1A-UNV-8CSB-VDIM
UPC	843654129006

## Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
----------------------	---

## Packaging

Carton	1
Weight Per each	10.14

## Uses, Certifications, and Standards

Energy Star	N
-------------	---