



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## FM1508 8' Fiberglass Mechanic Stepladder Type Ia

*Louisville Ladder*

|                  |   |
|------------------|---|
| Catalog Number   | FM1508  |
| Manufacturer     | Louisville Ladder   |
| Description      | Louisville; Twin Front Ladder; Type Ia; Ladder Height: 8 FT; Rung Size: 3 In; Base Size: 25-9/16 In Bottom Width; Material: Fiberglass; Load Capacity: 300 LB; Series: FM1500; Actual Cubic FT: 12.300 Cu-FT; Approx. Spread: 67-1/8 In |
| Weight per unit  | 34.0 (lbs/each)   |
| Product Category | Hand Tools - Ladders  |

### Features

|               |            |
|---------------|------------|
| Load Capacity | 94414      |
| Material      | Fiberglass |

### Descriptions

|                  |   |
|------------------|---|
| Description      | 8' FIBERGLASS MECHANIC STEPLADDER TYPE IA   |
| Long Description | Louisville; Twin Front Ladder; Type IA; Ladder Height: 8 FT; Rung Size: 3 IN; Base Size: 25-9/16 IN Bottom Width; Material: Fiberglass; Load Capacity: 300 LB; Series: FM1500; Actual Cubic Ft: 12.300 CU-FT; Approx. Spread: 67-1/8 IN |
| Product Type     | Twin Front Ladder, Louisville, Type Ia, Csa, Ansi A14.5, Osha, 8.0  |
| Special Features | Features: Da Boot For Slip Resistant Footing; Inside Spreader Braces; Double-Rivet Step Construction; Heavy Gauge Steel Hinges; Series: FM1500; Actual Cubic Ft: 12.300 CU-FT; Approx. Spread: 67-1/8 IN                                |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Louisville     |
| GTIN                      | 00728865088512 |
| Manufacturers Part Number | FM1508         |
| UPC                       | 728865088512   |

### Taxonomies, Classifications, and Categories

|                      |         |
|----------------------|---------|
| Category Description | LADDERS |
| Type                 | Type IA |

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 34 |

### Uses, Certifications, and Standards

|          |                       |
|----------|-----------------------|
| standard | CSA, ANSI A14.5, OSHA |
|----------|-----------------------|