



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FV0511VQL1 50/80/110 CFM Select DC Whisper Fan W/Led Light

Panasonic Corp Of N.A.

Catalog Number	FV0511VQL1
Manufacturer	Panasonic Corp Of N.A.
Description	Whisperceiling DC Fan With Led Light, Pick-A-Flow™ Speed Selector 50, 80 or 110 CFM With Ecm Motor, <0.3, <0.3, 0.4 Sone, 10W Led Chip Panel, <1W Led Night Light, Flex-Z Fast™ Installation Bracket, Integrated Dual 4" or 6" Duct Adaptor, 7-3/8" Housing Depth.
Weight per unit	11.2 (lbs/each)
Product Category	Exhaust Fans

Features

amperage rating	0.12-0.18
certification	HVI
Duct Shape	Round
Duct Size	4 or 6
Grill Size	13 x 13
Lamp Included	10 Watt Dimmable LED chip panel
Lamp Wattage	10
Material	Galvanized Steel
Power Rating	120/60
Voltage Rating	120
Warranty	6 years

Material, Color, and Finish

Blade Material	Plastic
Grill Material	Plastic
Housing Material	Zinc-Aluminum-Magnesium

Descriptions

Description	50/80/110 CFM SELECT DC WHISPER FAN W/LED LIGHT
extra long description	PEP FV-0511VQL1 WhisperCeiling Fan/
Long Description	WhisperCeiling DC fan with LED light, Pick-A-Flow™ Speed Selector 50, 80 or 110 CFM with ECM Motor, <0.3, <0.3, 0.4 sone, 10W LED Chip Panel, <1W LED night light, Flex-Z Fast™ installation bracket, Integrated dual 4" or 6" duct adaptor, 7-3/8" housing depth.
Product Type	Whisperceiling Fan/Light 50, 80, 110 CFM
Special Features	ECM Motor



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Whisperceiling DC
GTIN	00885170324954
Manufacturers Part Number	FV-0511VQL1
UPC	885170324954

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	Exhaust Fan

Packaging

Carton	1
Weight Per each	11.17

Uses, Certifications, and Standards

Application	Ventilation
Energy Star	yes
Frequency Rating	60
Mounting	Ceiling mount
standard	Pick-a-flow CFM,LED Lamp