



GAR6429, Mechanical Grounding Connector, Cable to Rod or Pipe

By Burndy
Catalog # [GAR6429](#)

Mechanical Grounding Connector, Cable to Rod or Pipe, 2/0 AWG (Sol) -250 kcmil, 3/8" Pipe, 5/8"-3/4" Rod, #5-#6 Rebar, Bright Dipped.



Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Direct Burial Cable, Fence Post

General

EU RoHS Indicator	Yes
Installation Torque Recommended in-lb	240 lb-in
Material	Copper Alloy
Material - Hardware Plated	DURIUM™ Silicon Bronze N
Plating Type	Bright Dipped
Sub Brand	MECHANICAL CONNECTOR
Type	GAR
U Bolt Type	269
UPC	781810238400
UPC 12 Digit	7818102384000

Dimensions

Dimension - B Length inch	1.75 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	46 mm
Dimension - Length Overall inch	1.81 in
Dimension - Outside Diameter inch	0.68 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.06 in
Dimension - Width mm	52 mm

Conductor Related

Conductor - Copper Solid Size	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Size Range	2/0 AWG - 250 kcmil
Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil
Conductor - Copper Str Size Range	1/0 AWG - 250 kcmil
Conductor - Copper Tube Std Size	3/8 IPS IPS
Conductor - Copper Tube Std Size Range	3/8 IPS IPS
Conductor - Pipe or Round Tube Size	3/8 in
Conductor - Rebar Size	5 ;6
Conductor - Rebar Size Range	5 -6
Conductor - Rod Size	0.625in - 0.75in
Conductor - Rod Size Range	5/8 in-3/4 in
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size• CU Tube Std-Size• Rod-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[3D Models - GAR6429_MODEL-IGES](#)
[3D Models - GAR6429_MODEL-PDF](#)
[3D Models - GAR6429_MODEL-STEP](#)
[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - SD_015789-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-GAR6429-SPEC-EN | REV 8/2023