



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GC2525CT 6-1/0 1-Bolt Ground Conn *Burndy LLC*

Catalog Number	GC2525CT
Manufacturer	Burndy LLC
Description	Cast Copper Alloy Cable Tray Ground Clamp, #6 Sol. (.162 Dia.) -1/0 STR. (.372 Dia.), 1.12 In L, 1.45 In W, Tin Plated.
Weight per unit	0.2400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	COPPER ALLOY
----------	--------------

Descriptions

Description	6-1/0 1-BOLT GROUND CONN
extra long description	BUR GC2525CT 6SOL-1/0 STR CABLETRAY
Long Description	Cast Copper Alloy Cable Tray Ground Clamp, #6 Sol. (.162 Dia.) -1/0 Str. (.372 Dia.), 1.12 in L, 1.45 in W, Tin Plated.
Product Type	Mechanical
Special Features	Features: Made Of Tin-Plated Cast Copper Alloy, It Accommodates Either One Or Two Conductors, Copper Or Aluminum Cable, In Addition To A Low Profile Head With A Deep Phillips Recess, The Galvanized Steel Bolt Has A Ribbed Neck Which Prevents Rotation During Installation When Installed In A 0.44 Diameter Hole, When Used On Aluminum Conductor, The Cable Must Be Scratch Brushed And PENETROX A Joint Compound Must Be Used On Cable And Connector, UL467 Listed For Copper Conductor Only, Suitable For Direct Burial

Manufacturer Information

Brand	BURNDY
GTIN	00781810035504
Manufacturers Part Number	GC2525CT
UPC	781810035504

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GC-CT

Packaging

Carton	1
Weight Per each	0.24



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Direct Burial Applications In Concrete Or Earth And For Used
With Aluminum Or Galvanized Steel Cable Tray

standard

UL467