



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **GAR194C #8SOL-#4STR to 2-1/2" Post Ground Conn**

*Burndy LLC*

Catalog Number	GAR194C
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 8 Awg (Sol.) - 4 Awg (STR.), 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe, Bright Dipped.
Weight per unit	N/A
Product Category	Large Terminals & Connectors

### **Features**

Material	Copper
----------	--------

### **Descriptions**

Description	#8SOL-#4STR TO 2-1/2" POST GROUND CONN
extra long description	BUR GAR194C 8-4CU 2 1/2IPS
Long Description	Mechanical Grounding Connector, Cable to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 2-1/2" to 2-7/8" Rod, 2-1/2" Pipe, Bright Dipped.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable, Parallel Or At Right Angles To Rod Or Tube, Especially Good For Fence Posts, High Copper Alloy Cast Body With DURIMUM U-Bolts, Nuts And Lockwashers, Permit Entire Connection To Be Buried In Ground Or Concrete Without Danger Of Corrosion, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial, Tube (ips) Size: 2-1/2 IN, Ground Rod Size: 2-1/2 - 2-7/8 IN, Width: 4-1/4 IN, Installation Torque: 240 IN-LB, Height: 5 IN

### **Manufacturer Information**

Brand	BURNDY
GTIN	00781810235607
Manufacturers Part Number	GAR194C
UPC	781810235607

### **Taxonomies, Classifications, and Categories**

Category Description	Fuses & Fuse Accessories
Type	GAR

### **Packaging**

Carton	1
Weight Per each	0



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Joining A Range Of Cable, Parallel Or At Right Angles To Rod  
Or Tube, Direct Burial Cable, Fence Post

standard

UL467