



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GFI11M139 Inline 15A/120V 2FT 12/3CORD Tri Tap Man

*Eaton Wiring Devices*

Catalog Number	GFI11M139
Manufacturer	Eaton Wiring Devices
Description	Eaton Portable Gfci, Watertight, Field Wireable 15A, #12 Awg, 2' (0.61M) Cord Length, Polycarbonate, 5-15, 3R, Tri Tap Plug Type, Manual Reset, 120V 669323
Weight per unit	0.3800 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

dimensions	3.0000 FT X 1.7200 IN X 1.9000 IN
------------	-----------------------------------

### Descriptions

Description	INLINE 15A/120V 2FT 12/3CORD TRI TAP MAN
extra long description	EWD GFI11M139 INLINE 15A/120V 2FT 1
Features	Eaton Arrow Hart portable ground fault circuit interrupters (GFCI) offer exceptional protection against electrical shock when connected to power generators, agricultural equipment, portable electric heaters, submersible pumps, industrial washers, outdoor signs and vending equipment. Features include a NEMA 4X rated housing for extreme conditions, dual indication lights which display power and fault status, and a variety of cord lengths.
Long Description	Eaton portable GFCI, Watertight, field wireable 15A, #12 AWG, 2' (0.61m) cord length, Polycarbonate, 5-15, 3R, Tri tap plug type, Manual reset, 120V 669323
Product Type	Inline 15A/120V 2FT 12/3CORD Tri Tap Man
Special Features	Portable GFCIs

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664669323
Manufacturers Part Number	GFI11M139
UPC	032664669323

### Taxonomies, Classifications, and Categories

Category Description	Industrial GFCI devices
Type	Portable GFCI

### Packaging

Carton	1
Package	25
Weight Per each	0.38



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application .....	Ind Facilities & Factories - Facility - Other .....
standard .....	cULus Listed,RoHS Compliant .....