



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GFRST20 20A Comm Self Test GFR Brown

Hubbell Wiring Devices

Catalog Number	GFRST20
Manufacturer	Hubbell Wiring Devices
Description	Hubbell Wiring Device Kellems, Power Protection Devices, Receptacle, Self Test, Gfci, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Weight per unit	0.3500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Terminal Screws
Number of Wires	3-Wire Grounding
pallet quantity	2240
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	2500
Wire Size	#14 to #12

Dimensions and Weight

Size	Standard Sized Product
------	------------------------

Descriptions

Description	20A COMM SELF TEST GFR BROWN
extra long description	HWDK GFRST20 20A COMM SELF TEST GFR
Features	AUTOGUARD® Self Test Technology 1st introduced by Hubbell over 10 years ago...self test monitoring now required in 2015 UL 943 GFCI Safety Standard... Hubbell AUTOGUARD® GFCI receptacles continually test and monitor for "people protection capability" automatically. This patented safety feature includes disconnecting power to the receptacle if critical components are damaged and GFCI protection is lost. GFCI auto-monitoring is conducted continuously within every 30 seconds. Also, clear visual indicators are pro
Long Description	Hubbell Wiring Device Kellems, Power Protection Devices, Receptacle,Self Test, GFCI, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R, Brown
Product Type	20A Comm Self Test GFR Brown
Special Features	Self-Test



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00883778122125
Manufacturers Part Number	GFRST20
series	Heavy Duty
UPC	883778122125

Taxonomies, Classifications, and Categories

Category Description	Commercial GFCI devices
Type	STANDARD

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.35

Uses, Certifications, and Standards

Application	Commercial Grade
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	Meets All NEC® Requirements