



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd  
78526-0000, TX Brownsville  
Phone: 956-295-3007  
Fax: 956-295-3008



## GBC210 10CKT Isol Ground Bar

*Nsi Industries*

Catalog Number	GBC210
Manufacturer	Nsi Industries
Description	The Nsi GBC2-10 Copper Isolated Ground Bar Mounts Onto Most Surfaces Using The High-Strength Glass-Filler Polyester Base, Then Fits Up to 10 Copper Cables In The 2 to 14 Awg Size Range. The High-Conductivity Copper Body Is Rated For Use With Copper Wiring and Forms Reliable Connections Using The Simple Tightening Screw Lug Design. Stock Products You Can Rely On
Weight per unit	1.4 (lbs/each)
Product Category	Ground Rods & Grounding System

### Features

Conductor Size	2-14 AWG
insulation	Glass Filled Polyester Base
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Conductor Material	Copper
--------------------	--------

### Dimensions and Weight

Length	4.07
Size	2-14 AWG



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5575 Ruben M Torres Blvd  
78526-0000, TX Brownsville  
Phone: 956-295-3007  
Fax: 956-295-3008

## Descriptions

Description	10CKT ISOL GROUND BAR
extra long description	NSI GBC2-10 Copper Isolated Ground
Features	NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These copper isolated grounding bars offer a convenient and reliable solution for grounding multiple copper cables. The high-conductivity copper bar and high-strength glass-filled polyester base are both designed for long-lasting performance in a variety of environments. Designed to fit a range of different wire sizes by using a screw lug design, these
Long Description	The NSI GBC2-10 Copper Isolated Ground Bar mounts onto most surfaces using the high-strength glass-filler polyester base, then fits up to 10 copper cables in the 2 to 14 AWG size range. The high-conductivity copper body is rated for use with copper wiring and forms reliable connections using the simple tightening screw lug design. Stock products you can rely on are stock NSI.
Product Type	Copper Isolated Ground Bar, 2-14 Awg Wire Range, 10 Circuit
Special Features	Copper Bar With Isolation Base - 10 Circuits

## Manufacturer Information

Brand	Polaris
GTIN	00662381010735
Manufacturers Part Number	GBC2-10
UPC	662381010735

## Taxonomies, Classifications, and Categories

Category Description	EXOTHERMIC GROUNDING PRODUCTS
Type	Isolated Ground Bars

## Packaging

Carton	1
Package	3
Weight Per each	1.4

## Uses, Certifications, and Standards

Application	Grounding Wire
-------------	----------------