



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GBC210 10CKT Isol Ground Bar

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GBC210 |
| Manufacturer | Nsi Industries |
| Description | The Nsi GBC2-10 Copper Isolated Ground Bar Mounts Onto Most Surfaces Using The High-Strength Glass-Filler Polyester Base, Then Fits Up to 10 Copper Cables In The 2 to 14 Awg Size Range. The High-Conductivity Copper Body Is Rated For Use With Copper Wiring and Forms Reliable Connections Using The Simple Tightening Screw Lug Design. Stock Products You Can Rely Onâ€”Stock Nsi. |
| Weight per unit | 1.4 (lbs/each) |
| Product Category | Ground Rods & Grounding System |

Features

| | |
|----------------|-----------------------------|
| Conductor Size | 2-14 AWG |
| insulation | Glass Filled Polyester Base |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------------------|--------|
| Conductor Material | Copper |
|--------------------|--------|

Dimensions and Weight

| | |
|--------|----------|
| Length | 4.07 |
| Size | 2-14 AWG |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 10CKT ISOL GROUND BAR |
| extra long description | NSI GBC2-10 Ground Bar CU 10 Circui |
| Features | NSI grounding and bonding products rise to the occasion in a wide variety of professional environments with excellent material quality and flexible designs. These copper isolated grounding bars offer a convenient and reliable solution for grounding multiple copper cables. The high-conductivity copper bar and high-strength glass-filled polyester base are both designed for long-lasting performance in a variety of environments. Designed to fit a range of different wire sizes by using a screw lug design, these |
| Long Description | The NSI GBC2-10 Copper Isolated Ground Bar mounts onto most surfaces using the high-strength glass-filler polyester base, then fits up to 10 copper cables in the 2 to 14 AWG size range. The high-conductivity copper body is rated for use with copper wiring and forms reliable connections using the simple tightening screw lug design. Stock products you can rely onâ€”stock NSI. |
| Product Type | Ground Bar Cu 10 Circuit 2-14 |
| Special Features | Copper Bar With Isolation Base - 10 Circuits |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381010735 |
| Manufacturers Part Number | GBC2-10 |
| UPC | 662381010735 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | EXOTHERMIC GROUNDING PRODUCTS |
| Type | Isolated Ground Bars |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 3 |
| Weight Per each | 1.4 |

Uses, Certifications, and Standards

| | |
|-------------|----------------|
| Application | Grounding Wire |
|-------------|----------------|