



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GD1829 250 Parallel Ground Conn

Burndy LLC

Catalog Number	GD1829
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 Awg (Sol.) - 250 Kcmil, 2" to 2-3/8" Rod, 2" Pipe.
Weight per unit	0.8700 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Copper Alloy, Cast
----------	--------------------

Descriptions

Description	250 PARALLEL GROUND CONN
extra long description	BUR GD1829 2/0-250 (2) CU 2.4 GRD
Long Description	Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 2/0 AWG (Sol.) - 250 kcmil, 2" to 2-3/8" Rod, 2" Pipe.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Ground Rod Size: 2 - 2-3/8 IN, Tube (ips) Size: 2 IN, Width: 3-3/4 IN, Installation Torque: 240 IN-LB, Height: 4-3/8 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810260333
Manufacturers Part Number	GD1829
UPC	781810260333

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GD

Packaging

Carton	1
Weight Per each	0.87



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

For Joining A Range Of Two Parallel Copper Cables To Rod Or
Pipe And Burial In Ground Or Concrete

standard

UL467