



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902



GHB1020 20A GHB 1P BKR *Eaton Corp*

| | |
|------------------|--|
| Catalog Number | GHB1020 |
| Manufacturer | Eaton Corp |
| Description | Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Single-Pole, 20A, 277 Vac, 125 VDC, 14 Kaic At 277 Vac, 50/60 HZ, 24 |
| Weight per unit | 0.6000 (lbs/each) |
| Product Category | 1 Pole |

Features

| | |
|------------------|-----------------------------------|
| Current Rating | 20 A |
| dimensions | 2.6300 IN X 1.0000 IN X 4.0000 IN |
| frame | G |
| interrupt rating | 14 kAIC at 277 Vac |
| media | Yes |
| Poles | Single-pole |
| Voltage Rating | 277 Vac, 125 Vdc |

Descriptions

| | |
|------------------------|---|
| Description | 20A GHB 1P BKR |
| extra long description | ETN GHB1020BP24 20A GHB 1P CB 4 KEY |
| Features | Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A. |
| Long Description | Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, fixed magnetic trip type, Single-pole, 20A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz, 24 |
| Product Type | 20A GHB 1P CB 4 Key Operated Attachment |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786679022030 |
| Manufacturers Part Number | GHB1020BP24 |
| UPC | 786679022030 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

121 S 39th Ave #100
85009-0000, AZ Phoenix
Phone: 480-372-4901
Fax: 480-372-4902

Taxonomies, Classifications, and Categories

Category Description PANELBOARD BRANCH BREAKERS
Type Molded case circuit breaker

Availability

Status Inactive

Packaging

Carton 1
Weight Per each 0.6

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & EOEM - Electrical Assemblies and
EOEMs - Other
standard UL Listed,Federal Specifications Classification W-C375B