



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville
72802-0000, AR Russellville
Phone: 479-967-2303
Fax: 479-967-2306



GL2038 2/0 1-Hole Compression Lug 3/8" Bolt

Nsi Industries

Catalog Number	GL2038
Manufacturer	Nsi Industries
Description	1 Holeshort Barrel Copper Compression Lug W/ PEEPHOLE2/0 Awg-3/8" Bolt Short Barrel Copper Compression Lugs With Peepholeis A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	0.0600 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Cable Size	2/0 AWG (STR)
Material	Copper
Number of Holes	1
Stud Size	3/8
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	Black
Finish	Tin Plated

Dimensions and Weight

Size	L=2.24 - W=.810 - OD=.560 - ID=.440
------	-------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1715 South Knoxville
72802-0000, AR Russellville
Phone: 479-967-2303
Fax: 479-967-2306

Descriptions

Description	2/0 1-HOLE COMPRESSION LUG 3/8" BOLT
extra long description	NSI GL2038 CU CMP Lug Short 2/0 AWG
Features	1 HoleShort Barrel Copper Compression Lug w/ PeepHole2/0 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	1 HoleShort Barrel Copper Compression Lug w/ PeepHole2/0 AWG-3/8" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	Cu CMP Lug Short 2/0 Awg 3/8 Bolt Size
Special Features	2/0 AWG (STR) - 3/8 Mounting Hole

Manufacturer Information

Brand	NSi
GTIN	00662381036094
Manufacturers Part Number	GL2038
UPC	662381036094

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - One Hole

Packaging

Carton	1
Package	25
Weight Per each	0.06

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	3/8 Mounting Hole
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)