



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GL6N141 #6 2H Cu SHRT CMP Lug

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GL6N141 |
| Manufacturer | Nsi Industries |
| Description | 2HOLESHORT Barrel Copper Compression Lug W/ PEEPHOLE6AWG-1/4" Bolt Short Barrel Copper Compression Lugs With Peepholeis A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit | 4.0 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|-----------------|---------------|
| Cable Size | # 6 AWG (STR) |
| Material | Copper |
| Number of Holes | 2 |
| Stud Size | 1/4 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Blue |
| Finish | Tin Plated |

Dimensions and Weight

| | |
|------|-------------------------------------|
| Size | L=2.09 - W=.420 - OD=.300 - ID=.200 |
|------|-------------------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | #6 2H CU SHRT CMP LUG |
| extra long description | NSI GL6N-141 CU CMP Lug Short 6 AWG |
| Features | 2HoleShort Barrel Copper Compression Lug w/ PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description | 2HoleShort Barrel Copper Compression Lug w/ PeepHole6AWG-1/4" Bolt Short Barrel Copper Compression Lugs with PeepHoleis a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type | Cu CMP Lug Short 6 Awg 1/4 Bolt 5/8 Spac |
| Special Features | # 6 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381338006 |
| Manufacturers Part Number | GL6N-141 |
| UPC | 662381338006 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Short Barrel - Two Hole |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 4 |

Uses, Certifications, and Standards

| | |
|--------------------------|---|
| Application | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C |
| Mounting | 1/4 Mounting Holes |
| standard | UL486A/B, UL467 (8 AWG -3/0 AWG) |