



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GRP11120 11" 120LB Natural CBL Tie

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GRP11120 |
| Manufacturer | Nsi Industries |
| Description | The Powergrp GRP-11120 100-Count Resealable Pack Of Type 21S Ah-2 Natural-Colored Heavy-Duty Cable Ties Are 11" Long, With 120LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 11" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) and 2.8" (71MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and S |
| Weight per unit | 2.6 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

Material, Color, and Finish

| | |
|--------|---------|
| Finish | Natural |
|--------|---------|

Descriptions

| | |
|------------------------|---|
| Description | 11" 120LB NATURAL CBL TIE |
| extra long description | NSI GRP-11120 PowerGRP Cbl Tie Natu |
| Features | PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-11120 ties combine a self-locking design with an industrial strength 120lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-11120 ties are water |
| Long Description | The PowerGRP GRP-11120 100-Count Resealable Pack of Type 21S AH-2 Natural-Colored Heavy-Duty Cable Ties are 11" long, with 120lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 11" cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) and 2.8" (71mm), using the bent tips and serrated locking mechanism to form an effortless and s |
| Product Type | Powergrp CBL Tie Natural 11" 120LB (100PK) |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381009319 |
| Manufacturers Part Number | GRP-11120 |
| UPC | 662381009319 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

Availability

| | |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 2.645 |

Uses, Certifications, and Standards

| | |
|--------------------|--------------|
| Temperature Rating | -40F to 185F |
|--------------------|--------------|