



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLL9 3-1/2" Mall Ins Ground Bushing

Crouse-Hinds

Catalog Number	GLL9
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLL Grounding Bushing, Rigid/Imc, Aluminum Lug, #3/0-6 Awg, Malleable Iron, 105°C Temperature Rating, Threaded, 3-1/2"
Weight per unit	1.1 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	4.9000 IN X 3.5000 IN X 7.3000 IN
Material	Malleable Iron Body, Plastic Throat Liner

Dimensions and Weight

Size	3-1/2 in
------	----------

Descriptions

Description	3-1/2" MALL INS GROUND BUSHING
extra long description	MIDWEST GLL 9 3 1/2 GRND BUSH 105C
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Aluminum lug, #3/0-6 AWG, Malleable iron, 105°C temperature rating, Threaded, 3-1/2"
Product Type	3 1/2 GRND Bush 105C Insul 3 to 6 Al Lug
Special Features	With 6 To 3/0 AWG Aluminum Lug for Copper/Aluminum Grounding Conductor, Weight 100 Lb per 100

Manufacturer Information

Brand	Eaton
GTIN	00784564123091
Manufacturers Part Number	GLL 9
UPC	784564123091

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Grounding bushing

Packaging

Carton	1
Weight Per each	1.05



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, CSA
Temperature Rating	105 DEG C