



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMA15R 15A 125V Fa 5X20MM Glass Fuse

Bussmann Fuses

| | |
|------------------|---|
| Catalog Number | GMA15R |
| Manufacturer | Bussmann Fuses |
| Description | Eaton Gma Series Fast-Acting Fuse, 15A, 125 Vac, 32 VDC |
| Weight per unit | 0.0020 (lbs/each) |
| Product Category | Small Dimension Fuses |

Features

| | |
|------------------|--|
| amperage rating | 15 A |
| connection | Ferrule End X Ferrule End |
| dimensions | X X 0.7874 IN |
| interrupt rating | 150 AIC at 125 Vac |
| Material | Glass tubeNickel-plated brass end cap construction |
| Response Time | 60 min at 135%, 2 min at 200% |
| Voltage Rating | 125 Vac, 32 Vdc |

Dimensions and Weight

| | |
|------|------------------------------------|
| Size | 5.20 mm Diameter X 20.00 mm Height |
|------|------------------------------------|

Descriptions

| | |
|------------------------|--|
| Description | 15A 125V FA 5X20MM GLASS FUSE |
| extra long description | BUSS GMA-15-R GMA 15A BUSS FUSE |
| Features | Fast-acting, glass tube 5 mm x 20 mm ferrule fuse designed to UL 248-14 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block or fuse clip. Also available with axial leads for thru-hole installation Eaton's GMA fast-acting, glass tube 5mm x 20mm ferrule fuses are designed to UL 248-14 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available |
| Long Description | Eaton GMA Series Fast-acting fuse, 15A, 125 Vac, 32 Vdc |
| Product Type | Gma 15A Buss Fuse |
| Special Features | Low Breaking Capacity, Interrupt Rating 150 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap, ROHS Compliant |

Manufacturer Information

| | |
|---------------------------|-----------------------|
| Brand | Eaton Bussmann series |
| GTIN | 00051712647878 |
| Manufacturers Part Number | GMA-15-R |
| UPC | 051712647878 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------------|
| Category Description | GLASS FUSES (and ceramic) |
| Type | Fast-Acting Fuse |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 5 |
| Weight Per each | 0.002 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Ind Facilities & Factories - Facility: Safety and Security Systems |
| standard | CE Marked, RoHS Compliant |