



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GRP14500X Cable Tie 14" 50LB BLK (1000PK)

Nsi Industries

|                  |  |
|------------------|--|
| Catalog Number   | GRP14500X  |
| Manufacturer     | Nsi Industries   |
| Description      | The Powergrp GRP-14500X 1000-Count Bulk Resealable Pack Of Type 21S Ah-2 Black-Colored General-Purpose Cable Ties Are 14" Long, With 50LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) and 4.02" (102MM), Using The Bent Tips and Serrated Locking Mechanism to Form An Effor |
| Weight per unit  | 5.3 (lbs/each)   |
| Product Category | Tools & Testers  |

### Features

|          |        |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | CABLE TIE 14" 50LB BLK (1000PK)  |
| extra long description | NSI GRP-14500X PowerGRP Cable Tie B  |
| Features               | PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-14500X ties combine a self-locking design with a general purpose 50lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-14500X ties are waterproof |
| Long Description       | The PowerGRP GRP-14500X 1000-Count Bulk Resealable Pack of Type 21S AH-2 Black-Colored General-Purpose Cable Ties are 14" long, with 50lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) and 4.02" (102mm), using the bent tips and serrated locking mechanism to form an effor        |
| Product Type           | Powergrp Cable Tie Black 14" 50LB (1000PK)   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381009647 |
| Manufacturers Part Number | GRP-14500X     |
| UPC                       | 662381009647   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 1000 |
| Weight Per each | 5.28 |

## Uses, Certifications, and Standards

|                    |              |
|--------------------|--------------|
| standard           | UL62275      |
| Temperature Rating | -40F to 185F |