



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GRP24175 24" 175LB HD Natural CBL Tie

Nsi Industries

| | |
|------------------|--|
| Catalog Number | GRP24175 |
| Manufacturer | Nsi Industries |
| Description | The Powergrp GRP-24175 50-Count Resealable Pack Of Type 21 Natural-Colored Super Heavy-Duty Cable Ties Are 24" Long, With 175LB Of Tensile Strength For Professional Applications. They're Made From Polyamide 6, 6 Nylon, Resulting In A High Mechanical Strength and A Wide Temperature Range (-40 F to 185 F). Fasten These 24" Cables Ties Around A Wide Range Of Equipment With A Bundle Diameter Between .28" (7MM) and 7.36" (187MM) Using The Bent Tips and Serrated Locking Mechanism to Form An Effortless and S |
| Weight per unit | 1.3 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|----------|--------|
| Warranty | 1 YEAR |
|----------|--------|

Material, Color, and Finish

| | |
|--------|---------|
| Finish | Natural |
|--------|---------|

Descriptions

| | |
|------------------------|---|
| Description | 24" 175LB HD NATURAL CBL TIE |
| extra long description | NSI GRP-24175 PowerGRP Cable Tie Na |
| Features | PowerGRP cable ties are a comprehensive product line of specialty ties, strong enough to handle industrial environments and ideally suited for demanding applications. The GRP-24175 ties combine a self-locking design with an industrial strength 175lb tensile strength rating, guaranteeing that these ties won't break easily. The GRP in our name stands for Guaranteed Rugged and Powerful, just one way we show that we're fully committed to building strong ties for professional users. GRP-24175 ties are water |
| Long Description | The PowerGRP GRP-24175 50-Count Resealable Pack of Type 21 Natural-Colored Super Heavy-Duty Cable Ties are 24" long, with 175lb of tensile strength for professional applications. They're made from polyamide 6,6 nylon, resulting in a high mechanical strength and a wide temperature range (-40 F to 185 F). Fasten these 24" cables ties around a wide range of equipment with a bundle diameter between .28" (7mm) and 7.36" (187mm) using the bent tips and serrated locking mechanism to form an effortless and s |
| Product Type | Powergrp Cable Tie Natural 24" 175LB (50PK) |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | NSi |
| GTIN | 00662381009432 |
| Manufacturers Part Number | GRP-24175 |
| UPC | 662381009432 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
|----------------------|--|

Availability

| | |
|-------------|----|
| minimum qty | 50 |
|-------------|----|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 1.25 |

Uses, Certifications, and Standards

| | |
|--------------------|--------------|
| standard | UL62275 |
| Temperature Rating | -40F to 185F |